

OMA



OPTICAL MODULATION ANALYZER

SPECIFICATION SHEET

Get the most out of your investment with Tektronix oscilloscope's scalable architecture. Use the stack as a single 70 GHz OMA system today then use it as four independent oscilloscopes tomorrow.




Built-in narrow linewidth tunable laser

IQRX comes with a built-in narrow 25 KHz instantaneous linewidth laser, making it perfect for coherent modulation formats that require high phase stability.




VISIQ™ - feature-rich OMA software

VISIQ's superior user interface offers comprehensive visualization for ease-of-use combined with the power of MATLAB®.




Multi-system configuration

Simultaneously displays data from multiple OMAs at same or different wavelengths, simplifying multi-channel measurements.




Full characterization of coherent modulation formats

Complete coherent signal analysis for polarization-multiplexed QPSK, QAM, differential BPSK/QPSK, and other advanced modulation formats.




Dual polarization measurement

IQRX houses polarization selective hardware to characterize polarization multiplexed signals. LO input, signal input and internal laser outputs all use polarization maintaining (PM) fiber for the highest versatility.




High-performance, low-noise coherent receiver

IQRX is the gold standard coherent receiver with market-leading performance. It is designed and built using the highest-performing discrete fiber optic components to provide superior fidelity measurement of coherently modulated signals.



Superchannel measurement made simple

Superchannel configuration allows you to define number of channels, channel frequency, and channel modulation format.



19 inch rack mountable

IQRX can be paired with the rack mount brackets for easy mounting in any 19 inch rack.

The industry's most flexible OMA system

Whether you are working with 100G coherent transceivers or 1 Terabit long haul communication systems, our OMA can be configured to suit your exact requirements.


- Up to 70GHz of system bandwidth
- Characterize 400ZR and 800ZR signals up to 140GBaud
- Supports single and dual polarization PSK and QAM formats
- Visual signal analysis using constellation and eye diagrams
- Performance parameter measurement including EVM, BER, Bias errors and more
- Two built-in narrow linewidth tunable lasers for receiver hardware self-calibration




TARGET APPLICATIONS

- Coherent DSP development
- Coherent transmitter testing
- Custom modulation format development
- Mil / Aero communications R&D

OMA SCHEMATIC DIAGRAM



A SCALABLE SYSTEM THAT GROWS WITH YOUR NEEDS



SCALABLE CONFIGURATION TO MATCH YOUR REQUIREMENTS

Max Baud Rate / System Bandwidth

26 GBaud dual pol 13 GHz BW	32 GBaud dual pol 16 GHz BW	46 GBaud dual pol 23 GHz BW	66 GBaud dual pol 33 GHz BW	100 GBaud dual pol 50 GHz BW	140 GBaud dual pol 70 GHz BW
--------------------------------	--------------------------------	--------------------------------	--------------------------------	---------------------------------	---------------------------------

Configuration: Coherent Receiver

IQRX-1002



IQRX-1004



Configuration Scope: (Bandwidth upgradable)

DP071304SX



DP071604SX




DP072304SX




DPS73308SX



2x DPS75004SX




2x DPS77004SX



Thanks to the modular architecture of DPO70000SX series oscilloscopes, you can decouple some of the oscilloscopes to use for direct measurement, when not in use as an OMA system.

Coherent & PAM4/NRZ Solutions




The VISIQ Optical Modulation Analysis (OMA) software provides an ideal platform for research and testing of coherent optical systems.

VISIQ is designed to make coherent signal analysis and DSP optimization as simple as possible. It features an intuitive user-interface that reduces the learning curve for new users, while still providing the ability for advanced users to fully customize the signal processing algorithms.

Easy-to-use, intuitive GUI


The modern user interface provides an intuitive presentation of the configuration & analysis workflow to make the coherent DSP simple to understand and use.

1. Show/hide system menu
2. Configuration menu
3. Configuration control panel
4. Data acquisition control
5. Visualization area
6. Analysis measurements table
7. Signal summary panel
8. Connection status




Auto-discovery of hardware

VISIQ automatically discovers compatible coherent receiver and oscilloscope hardware on the USB or ethernet network for a hassle-free setup.




Integrated hardware control

Control oscilloscopes, coherent receivers and the internal lasers within VISIQ's software interface, so you do not need to switch between multiple software applications.




Powerful adaptive equalizers

The advanced equalizer algorithm can be set to train over multiple iterations to test the boundaries of DSP signal optimization and boost test efficiency.




Dynamic CoRx auto-calibration

Automatic receiver calibration algorithm detects receiver IQ skew, gain imbalance and DC offset from the measured signal to remove them on-the-fly. This ensures that the OMA hardware calibration is always finely tuned so that every measurement is accurate and repeatable.




On-the-fly adjustment of DSP parameters

Modify DSP parameters while running in continuous acquisition mode for instant feedback. Use VISIQ as an educational tool where you can instantly see the impact of each functional DSP node to aide users' understanding.




Save, recall and replay measurements

Conveniently save projects, graphs or series of raw waveforms and play them back for offline processing. Playing back saved waveforms allows full reconfiguration of DSP for future troubleshooting or sharing of measurement with others.



Modular MATLAB integration

Import your own MATLAB algorithm into the reconfigurable nodal DSP pipeline, giving you the freedom to place your code anywhere within the DSP chain. Replace just one functional DSP node, or bring in the whole DSP code. With the flexible placement of custom MATLAB node within the pipeline, the possibilities are endless.



Supports SCPI and gRPC remote control


In addition to the intuitive GUI, VISIQ supports test automation via SCPI and GRPC command support.

Command	:PROJect:SOURce:DATA:SIGNal:BAUDrate?	Summary >>
Syntax	:PROJect:SOURce:DATA:SIGNal:BAUDrate? [<wsp><SET UNIT STEP ACT ALL>]	
Description	Query the Baud rate of the signal	
Parameters	None: Returns the currently set value in the default unit SET : Returns the currently set value in the default unit UNIT : Returns the measurement unit STEP : Returns the resolution/step size of settable values. STEP = 1 allows values of 1, 2, 3. STEP = 0.1 allows values of 1.1, 1.2, 1.3 etc. ACT : Returns the currently set value in the default unit ALL : Returns all the above parameters in a comma-separated string: <SET>, <UNIT>, <STEP>, <ACT>	
Response	A single value, or a comma-separated array of values	
Example	:PROJ:SOUR:DATA:SIGN:BAUD? -> 59843750000.000000	

Command	:PROJect:SOURce:DATA:SIGNal:BAUDrate	Summary >>
Syntax	:PROJect:SOURce:DATA:SIGNal:BAUDrate<wsp><value>	
Description	Set the Baud rate of the signal	
Parameters	<value>: Sets this value	
Response	N/A	
Example	:PROJ:SOUR:DATA:SIGN:BAUD 59843750000 :PROJ:SOUR:DATA:SIGN:BAUD 59843750 KBAUD :PROJ:SOUR:DATA:SIGN:BAUD 59843.75 MBAUD :PROJ:SOUR:DATA:SIGN:BAUD 59.84375 GBAUD	

Screenshot-friendly signal summary

The signal summary bar enables an effective documentation by recording key signal information in every screen capture.



OMA TECHNICAL SPECIFICATIONS

General Specifications	IQRX
Dimensions (H x W x D)	44.1 x 440 x 528 mm 1.74 x 17.32 x 20.79 inch
Weight	~ 9.2 kg ~ 20.3 lbs
Operating temperature range	5 °C to 45 °C 41 °F to 113 °F
Storage temperature range	-40 °C to 70 °C -40 °F to 158 °F

Model Number	1002	1004
Operating wavelength range	1527 to 1630 nm	
Number of polarizations	2	
RF outputs	4: Xi, Xq, Yi, Yq	
Optical connector type	FC/PC, FC/APC	
Coherent receiver RF connector type	2.4 mm female	1.85 mm female
Photodetector bandwidth (-3 dB) ¹	> 45 GHz (Typical)	> 70 GHz (Typical)
RF impedance	50 ohms	
Low frequency cutoff	0 Hz	
Damage level external LO input	+ 25 dBm	
Damage level signal input	+ 25 dBm	
Polarization extinction ratio LO input	> 20 dB	

System Specifications	IQRX-1002 + DPO73304SX 33GHZ OSCILLOSCOPES	IQRX-1004 + DPO77002SX 70GHZ OSCILLOSCOPES
Maximum detectable symbol rate	66 GBaud	140 GBaud
System bandwidth ²	33 GHz	70 GHz
Oscilloscope sensitivity range	62.5 mVfs to 6 Vfs	100 mVfs to 300 mVfs
Record length (standard)	62.5 M/Ch	62.5 M/Ch
Extended record length (optional)	1 G/Ch	1 G/Ch
Oscilloscope sample rate	100 GS/s	200 GS/s
ADC resolution	8 bits	8 bits
Relative skew after correction ²	< ± 0.5 ps	< ± 0.5 ps
Quadrature error after correction ²	< ± 0.5°	< ± 0.5°
EVM noise floor ³	< 1.3% at 2.5GHz, < 1.8% at 10GHz	< 1.3% at 2.5GHz, < 1.8% at 10GHz
Image suppression ratio ³	> 40 dB	> 40 dB

OMA TECHNICAL SPECIFICATIONS


Internal Laser Specifications	1002	1004
Number of internal lasers	2	
Maximum optical CW output power	+ 15.0 dBm	
Minimum optical CW output power	+ 8 dBm	
Internal laser wavelength tuning range	1527.60 to 1568.70 nm	
Minimum wavelength step	~1 ppm	
Minimum frequency step	100 MHz	
Tuning time/sweep speed	< 30 s	
Absolute wavelength accuracy	10 ppm	
Linewidth (short term)	< 100 kHz, 25 kHz (Typical)	
Sidemode Suppression Ratio (SMSR)	55 dB (Typical)	
Relative Intensity Noise (RIN)	- 145 dB/Hz (10 MHz to 40 GHz)	

Notes

All specifications are subject to change without notice.

1. Bandwidth of individual photodetectors in balanced pair.
2. When paired with DPO70000SX series oscilloscopes. Digitally compensated.
3. Test conditions: Dual polarization, 13GHz channel bandwidth, 2.5GHz or 10GHz frequency offset, 13.5dBm LO input power, 8.0dBm signal input power, Viterbi & Viterbi phase estimation.

Instrument dimensions



Rear panel connections




SYSTEM REQUIREMENTS

- Operating system: Microsoft Windows® 10 (64-bit)
- Processor: Intel® Core™ i5 or faster CPU
- Memory: 8 GB or greater

Note: VISIQ offers MATLAB custom code integration. In order to use this feature, a licensed copy of MATLAB must be installed on the PC.

ORDERING INFORMATION



Individual oscilloscopes

DPO77002SX = ATI performance oscilloscope with 1 Ch x 70 GHz, 200 GS/s or 2 Ch x 33 GHz, 100 GS/s
DPO75902SX = ATI performance oscilloscope with 1 Ch x 59 GHz, 200 GS/s or 2 Ch x 33 GHz, 100 GS/s
DPO75002SX = ATI performance oscilloscope with 1 Ch x 50 GHz, 200 GS/s or 2 Ch x 33 GHz, 100 GS/s
DPO73304SX = Digital phosphor oscilloscope with 2 Ch x 33 GHz, 100 GS/s or 4 Ch x 23 GHz, 50 GS/s
DPO72304SX = Digital phosphor oscilloscope with 2 Ch x 23 GHz, 100 GS/s or 4 Ch x 23 GHz, 50 GS/s

Multi-unit systems

DPS77004SX = 70GHz ATI Performance Oscilloscope System: 2 Ch x 70 GHz, 200 GS/s or 4 Ch x 33 GHz, 100 GS/s
DPS75904SX = 59GHz ATI Performance Oscilloscope System: 2 Ch x 59 GHz, 200 GS/s or 4 Ch x 33 GHz, 100 GS/s
DPS75004SX = 50GHz ATI Performance Oscilloscope System: 2 Ch x 50 GHz, 200 GS/s or 4 Ch x 33 GHz, 100 GS/s
DPS73308SX = 33GHz Digital Phosphor Oscilloscope System: 4 Ch x 33 GHz, 100 GS/s or 8 Ch x 23 GHz, 50 GS/s

WARRANTY INFORMATION

This product comes with a standard 1 year warranty.

EXTENDED WARRANTIES AND CALIBRATION PLANS

With an **extended warranty and calibration plan** you'll spend more time focused on your priorities and less time worrying about maintenance.

Your choice: add a **3 or 5 year extended warranty** when you buy.



Guarantee performance

Ensure your equipment is operating at the best it can be for reliable and accurate results.

Lower cost of ownership

Lock in savings and maximise your testing budget with a lower base cost of ownership.

Peace of mind

Spend less time worrying about maintenance and more on generating results.

CALIBRATION PLANS FOR ADDITIONAL DISCOUNTS

Order a **calibration plan** when purchasing your Quantifi Photonics instruments and get additional discounts.

10% Discount

On calibrations ordered at the time of purchase.

25% Discount

Add on an extended warranty and receive a 25% discount on calibrations.

Over time and with regular use, all optical parts and connectors require re-calibration and maintenance to guarantee accurate and reliable performance. We recommend Quantifi Photonics optical instruments are re-calibrated every 12 months. With an instrument calibration performed by Quantifi Photonics technicians you receive:

- Comprehensive calibration to factory specifications
- End-to-end inspection to ensure all instrument functions are working and connectors are clean
- Firmware, software and documentation updates
- Certificate of calibration which includes detailed test results

How to do I secure my extended warranty or calibration plan?

Contact your Quantifi Photonics sales representative or email sales@quantifiphotonics.com

Extended warranties and calibration plans must be ordered at the time of purchase and are available only for Quantifi Photonics' products. The 25% calibration discount only applies to calibrations while the product is covered by the extended warranty period.

Our portfolio of optical & electro-optical test modules is rapidly expanding to meet a wide range of customer requirements and applications.

Tunable Laser Sources

Versatile telecom laser sources with full tunability across C or L bands. Narrow 100 kHz linewidth, up to 16.5 dBm of power, optional whisper mode to disable frequency dither.



Fixed Wavelength Laser Sources

Highly customizable laser platform. Select required wavelength, power and fiber type for a customized solution.



Swept, Tunable Continuous Wave Laser

Swept, tunable continuous wave (CW) laser source with 0.01 dB power stability and 400 nm/s high-speed scan rate for R&D and production testing.



Superluminescent Diode Broadband Light Source

Super-luminescent LED light source with high output power, large bandwidth and low spectral ripple and various wavelengths.



Optical-to-Electrical Converter

High bandwidth, broadband O-to-E converter. Available in a range of configurations; choose from 1 or 2 channels, AC or DC coupling and various conversion gain and operating wavelength ranges.



Variable Optical Attenuator (VOA)

Fast attenuation speed with low insertion loss and built-in power monitoring. Operates in fixed attenuation or constant output power modes. Models support SMF, MMF and PMF connector types.



Polarization Controller & Scrambler

High-speed automated polarization control with broad wavelength coverage from 1260nm to 1650nm, low insertion loss and back reflection. Full remote control via intuitive GUI, LabVIEW or SCPI.



Optical Power Meters

Fast terminating or inline monitoring of optical signal power from -60 to +10 dBm across 750 – 1700 nm wavelengths. Model with logarithmic analog output for applications such as silicon photonics fiber alignment.



Optical Spectrum Analyzer (OSA)

Cost-effective, spectral measurement in a compact module with built-in analysis for: SMSR, OSNR & spectral width. Targeted wavelengths for specific applications in O band, C band & L band.



Digital Sampling Oscilloscope (DSO)

Digital equivalent-time sampling oscilloscope (DSO) with high-quality precision timebase and low jitter mode, available in 1 or 2 channels in a compact benchtop instrument.



Bit Error Rate Tester (BERT)

4 or 8-channel Pulse Pattern Generator and Error Detector at rates up to 29 Gbps for the design, characterization and production of optical transceivers and opto-electrical components.



Passive Component Integration

Integrate passive optical components of your choice such as WDM couplers, splitters, band-pass filters, PM beamsplitters and circulators. Models support SMF, MMF and PMF.



Photonic Doppler Velocimeter (PDV)

Purpose-built module for Photonic Doppler Velocimetry (PDV). A circulator, two VOAs and a passive coupler all built into one compact module.



Optical Switch

Proven reliability and fast switching time. Wide variety of switch configurations: 1x4, 1x16, 16x16 and more. Models support SMF, MMF and PMF.



Passive Component Storage

Protect and store your own passive fiber optic components such as splitters, connector adaptor patchcords, WDM couplers, and isolators in one handy module.



For more details visit quantifiphotonics.com/products

Test. Measure. Solve.TM

Quantifi Photonics is transforming the world of photonics test and measurement. Our portfolio of optical and electrical test instruments is rapidly expanding to meet the needs of engineers and scientists around the globe. From enabling ground-breaking experiments to driving highly efficient production testing, you'll find us working with customers to solve complex problems with experience and innovation.

To find out more, get in touch with us today.

General Enquiries	sales@quantifiphotonics.com
Technical Support	support@quantifiphotonics.com
Phone - NZ	+64 9 478 4849
Phone - USA	+1-800-803-8872

quantifiphotonics.com

**QUANTIFI
PHOTONICS®**

Quantifi Photonics Ltd © 2024. All rights reserved. No part of this publication may be reproduced, adapted, or translated in any form or by any means without the prior permission from Quantifi Photonics Ltd. All specifications are subject to change without notice. Please contact Quantifi Photonics for the latest information.